




FOCAL LENGTH (EFL): $5 \pm 0,05$

BACK FOCAL LENGTH (BFL): 3,96

- 1 AR COATING: VIS-NIR
 $R(ABS) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$4,02 \pm 0,004$ CX	GLASS N-LaSF44 803/464	R	∞ PL
Øe	4,5		Øe	4,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	56,04'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

5,0mm Dia, x 5,0mm FL, VIS-NIR, Inked,
Plano-Convex Lens

DWG NO

478571NK

SHEET SIZE
A4

SHEET
1 OF 1