




FOCAL LENGTH (EFL): 24 ± 0,24
BACK FOCAL LENGTH (BFL): 23,13

- 1 AR COATING: NIR I
R(AVG) ≤ 0,5% FROM 600-1050nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	24,36±0,024 CX	GLASS N-BK7 517/642	R	24,36±0,024 CX
Øe	5,4		Øe	5,4
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

6mm Dia, x 24mm FL, NIR I, Inked,
Double-Convex Lens

DWG NO

494611NK

SHEET SIZE
A4

SHEET
1 OF 1