





FOCAL LENGTH (EFL): $80 \pm 0,8$

BACK FOCAL LENGTH (BFL): 77,95

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	36,68±0,037 CX		GLASS FUSED SILICA 458/678	R	∞ PL	
Øe	19			Øe	19	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	2,18'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT		SCALE: NONE				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				20mm Dia, x 80mm FL Uncoated, UV Plano-Convex Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	49964
			SHEET SIZE			SHEET
			A4			1 OF 1