



FOCAL LENGTH (EFL): 30 ±0,3
 BACK FOCAL LENGTH (BFL): 28,77

- 1 AR COATING: UV-VIS
 R(AVG) ≤ 1,5% FROM 250-700nm @ 0° AOI
 R(ABS) ≤ 1,0% FROM 350-450nm @ 0° AOI

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|--------------------------|----------------------------|---------------|--------------------------|
| R | 26,943±0,027 CX | GLASS FUSED SILICA 458/678 | R | 26,943±0,027 CX |
| Øe | 11 | | Øe | 11 |
| 3/ | 3 (0,5) λ=632,8 nm | | 3/ | 3 (0,5) λ=632,8 nm |
| 4/ | - | | 4/ | 2,18' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

| | | | | |
|--|-------------------------|---|--|--|
| PROTECTIVE CHAMFERS AS NEEDED | | FIRST ANGLE PROJECTION |  | |
| ROHS: COMPLIANT | SCALE: NONE λ = 587,6nm | | | |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY | |  | TITLE | 12mm Dia, x 30mm, UV-VIS Coated, UV Double-Convex Lens |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING | | | ALL DIMS IN: mm | DWG NO |
| INDICATIONS IN ACCORDANCE WITH ISO 10110 | | | SHEET SIZE | A4 |
| | | | | SHEET 1 OF 1 |