





FOCAL LENGTH (EFL): 45 ± 0.45
 BACK FOCAL LENGTH (BFL): 43.96

1 AR COATING: UV-VIS
 R(AVG) ≤ 1.5% FROM 250-700nm @ 0° AOI
 R(ABS) ≤ 1.0% FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	40,785±0,041 CX	GLASS FUSED SILICA 458/678	R	40,785±0,041 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 12mm Dia, x 45mm, UV-VIS Coated, UV Double-Convex Lens					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm					DWG NO 48838		SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING										
INDICATIONS IN ACCORDANCE WITH ISO 10110										