




FOCAL LENGTH (EFL): $9 \pm 0,09$

BACK FOCAL LENGTH (BFL): 7,29

1 AR COATING: VIS 0°
 $R(\text{AVG}) \leq 0,4\%$ FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$4,13 \pm 0,004$ CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	6,55'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

6mm Dia, x 9mm FL VIS 0 Coated, UV
Plano-Convex Lens

DWG NO

48944

SHEET SIZE
A4

SHEET
1 OF 1