




FOCAL LENGTH (EFL): $15 \pm 0,15$

BACK FOCAL LENGTH (BFL): 14,33

1 AR COATING: VIS 0°
R(AVG) $\leq 0,4\%$ FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	15,16 $\pm$ 0,015 CX	GLASS N-BK7 517/642	R	15,16 $\pm$ 0,015 CX
Øe	4,5		Øe	4,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

5mm Dia, x 15mm FL, VIS 0 Coated,
Double-Convex Lens

DWG NO

63596

SHEET SIZE
A4

SHEET
1 OF 1