



FOCAL LENGTH (EFL):  $4 \pm 0,04$   
 BACK FOCAL LENGTH (BFL): 3,57

1 AR COATING:  
 $\frac{1}{4}$  WAVE MgF2 @ 550nm  
 R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$3,4 \pm 0,003$ CX	GLASS N-LaSF9 850/322	R	$\infty$ PL
Øe	1,5		Øe	1,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	<b>Edmund Optics®</b>		
ROHS: COMPLIANT	SCALE: NONE				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	2,0mm Dia, x 4,0mm FL, MgF2 Coated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	65267
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	SHEET 1 OF 1