





FOCAL LENGTH (EFL): 75 ±0,75
BACK FOCAL LENGTH (BFL): 71,96

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE			
R	34,385±0,034 CX		GLASS FUSED SILICA 458/678	R	∞ PL		
Øe	24			Øe	24		
3/	2 (0,2) λ=632,8 nm			3/	2 (0,2) λ=632,8 nm		
4/	-			4/	2,18'		
5/	20 - 10 (MIL-PRF-13830B)			5/	20 - 10 (MIL-PRF-13830B)		
6/	-			6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25mm Diameter x 75mm FL, Uncoated, Laser Grade PCX Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	67096	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm			