




FOCAL LENGTH (EFL): 200 ±2

BACK FOCAL LENGTH (BFL): 195,19

- 1 AR COATING: UV-VIS
 $R(AVG) \leq 1,5\%$ FROM 250-700nm @ 0° AOI
 $R(ABS) \leq 1,0\%$ FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	91,69±0,092 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	49		Øe	49
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

50mm Dia, x 200mm FL UV-VIS Coated,
UV Plano-Convex Lens

DWG NO

67231

SHEET SIZE
A4

SHEET
1 OF 1