




FOCAL LENGTH (EFL): 120 ±1,2
BACK FOCAL LENGTH (BFL): 116,57

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	55,016±0,055 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	29		Øe	29
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

30mm Dia, x 120mm FL Uncoated, UV
Plano-Convex Lens

DWG NO

84285

SHEET SIZE
A4

SHEET
1 OF 1