




FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $17,07$

- 1 AR COATING: VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350-700nm @ 0° AOI
 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$9,3 \pm 0,009$ CX	GLASS N-BK7 517/642	R	∞ PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

6,0mm Dia, x 18,0mm FL, VIS-EXT, Inked, Plano-Convex Lens

DWG NO

88642INK

SHEET SIZE
A4

SHEET
1 OF 1