

FOCAL LENGTH (EFL):  $72 \pm 0,72$

BACK FOCAL LENGTH (BFL): 70,68

1 AR COATING: 532nm V-COAT  
 $R(\text{ABS}) < 0,25\% @ 532\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	37,21±0,037 CX	GLASS N-BK7 517/642	R	$\infty$ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 9,0mm Diameter x 72,0mm FL, 532nm V-Coat, PCX Lens

DWG NO 69376

SHEET SIZE A4  
 SHEET 1 OF 1