



FOCAL LENGTH (EFL):  $18 \pm 0,18$   
 BACK FOCAL LENGTH (BFL):  $17,26$

1 AR COATING: VIS-EXT  
 $R(AVG) \leq 0,5\%$  FROM 350-700nm @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$18,22 \pm 0,018$ CX	GLASS N-BK7 517/642	R	$18,22 \pm 0,018$ CX
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 6mm Dia, x 18mm FL, VIS-EXT Coated, Double-Convex Lens

DWG NO 89132

SHEET SIZE A4 SHEET 1 OF 1