




FOCAL LENGTH (EFL): $6 \pm 0,06$

BACK FOCAL LENGTH (BFL): 5,19

- 1 AR COATING: YAG-BBAR
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$
 $R(AVG) < 1,0\% FROM 500-1100nm @ 0^\circ AOI$
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$7,59 \pm 0,008 CX$	GLASS N-SF5 673/322	R	$7,59 \pm 0,008 CX$
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda = 632,8 nm$		3/	3 (0,5) $\lambda = 632,8 nm$
4/	-		4/	4,46'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
SCALE: NONE $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

6mm Dia, x 6mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens

DWG NO

89216INK

SHEET SIZE
A4

SHEET
1 OF 1