




FOCAL LENGTH (EFL):  $48 \pm 0,48$   
 BACK FOCAL LENGTH (BFL):  $47,09$

1 AR COATING: VIS-EXT  
 $R(AVG) \leq 0,5\%$  FROM 350-700nm @  $0^\circ$  AOI

| LEFT SURFACE |                            | MATERIAL            | RIGHT SURFACE |                            |
|--------------|----------------------------|---------------------|---------------|----------------------------|
| R            | $49,14 \pm 0,049$ CX       | GLASS N-BK7 517/642 | R             | $49,14 \pm 0,049$ CX       |
| Øe           | 11                         |                     | Øe            | 11                         |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                     | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                     | 4/            | 1,93'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                     | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                     | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12mm Dia, x 48mm FL, VIS-EXT Coated, Double-Convex Lens

DWG NO

89155

SHEET SIZE  
A4

SHEET  
1 OF 1