


NOTES:
 1. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

DESIGN WAVELENGTH(nm)	670.00
OUTPUT POWER (mW)	3.0 (Maximum)
BEAM DIAMETER (mm)	4 x 2
FOCUS RANGE	35mm - ∞
COLOR	Red
LASER CLASS - CDRH	IIIa
MEAN TIM TO FAILURE @ 25° (HOURS)	>20,000
POINTING ACCURACY (mrad)	<25
POWER REQUIREMENT	3.5 - 5 V DC
TYPE	Index Guided Diode, CW

EO® Edmund Optics®



TITLE	3.0mW 670nm, MINIATURE LDM LASER DIODE		
DWG NO	53233	SHEET 1 OF 1	

ALL DIMS IN

mm