




FOCAL LENGTH (EFL): 200 ±2

BACK FOCAL LENGTH (BFL): 197,89



LEFT SURFACE AR COATING:

VIS 0°

R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

RIGHT SURFACE AR COATING:

VIS 0°

R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	103,36 CX	GLASS N-BK7 Nd: 1,517 Vd: 64,2	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20		5/	40 - 20
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



ALL DIMS
IN:

mm



Edmund Optics®

TITLE

15mm Dia x 200mm FL, VIS 0 Coated,
Plano-Convex Lens

DWG NO

14376

SHEET
SIZE

A4

SHEET
1 OF 1

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110