


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


334nm Bandpass Interference Filter: 10nm FWHM, OD >3.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


365nm Bandpass Interference Filter: 10nm FWHM, OD >3.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

405nm Bandpass Interference Filter: 10nm FWHM, OD $\geq$ 3.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

436nm Bandpass Interference Filter: 10nm FWHM, OD $\geq$ 3.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


546nm Bandpass Interference Filter: 10nm FWHM, OD $\geq$ 3.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


**250nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance
FOR REFERENCE ONLY**



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


265nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


280nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


289nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


297nm Bandpass Interference Filter: 10nm FWHM, OD ≥ 4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

313nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

577nm Bandpass Interference Filter: 10nm FWHM, OD >4.0 Coating Performance FOR REFERENCE ONLY

