



NOTES:

1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: 74
4. SAMPLED ANGLE: 2.0 x 2.0
5. COATING:
LASER V-COAT (532nm)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 0.18mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

| | | | | | | | |
|--------------------|----------------------|----------------------|------------------------|--|-------------|---|--------|
| | S1 | S2 | THIRD ANGLE PROJECTION | | TITLE | 532nm, 11mm Dia., 5x5 SPOT MATRIX, DIFFRACTIVE BEAMSPLITTER | |
| SHAPE | PLANO | PLANO | | | ALL DIMS IN | mm | DWG NO |
| MIN CLEAR APERTURE | Ø9.2 | Ø9.2 | | | | | |
| BEVEL MAX FACE | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | | | | |