



NOTES:

1. SUBSTRATE: ZINC SELENIDE (ZnSe)
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: 79
4. SAMPLED ANGLE: 2.70
5. COATING:  
LASER V-COAT (10.6µm)
6. BEAM SPECIFICATION:  
MINIMUM BEAM DIAMETER: 1.35mm



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	10600nm, 27.94mm Dia., 1x2 SPOT ARRAY, DIFFRACTIVE BEAMSPLITTER	
SHAPE	PLANO	PLANO			DWG NO	14694	SHEET
MIN CLEAR APERTURE	Ø25.1	Ø25.1	ALL DIMS IN	mm			
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					