



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

NOTES:


1. SUBSTRATE: ISUZU ISK167  
DENSITY: 2.62g/cm³  
REFLECTION FACTOR: 0.92  
KNOOP HARDNESS: 502kg/mm²  
REFRACTIVE INDEX: 1.52nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø11.25
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN      mm

 **Edmund Optics®**

TITLE	ISUZU ISK167, 12.5 Dia., HEAT ABSORBING COLORED GLASS FILTER	
DWG NO	15701	SHEET 1 OF 1