NOTES:

- 1. SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):


\$1, \$2, \$3, & \$4: R(AVG) <0.5% @ 430 - 670nm \$5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 65% ± 5%


POLARIZATION < 6%

FINE GROUND SURFACE

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

/6.\ MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM





FOR INFORMATION ONLY:

PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

S1	
5 .	S2
SHAPE PLANO PI	_ANO
surface accuracy \\ \lambda/8	λ/8
SURFACE QUALITY 40-20 4	0-20
CLEAR APERTURE > 90%	90%

			Edmund Option	CS®
THIRD ANGLE _ PROJECTION		TITLE	20mm VIS, 30R/70T, Non-Polarizing C Beamsplitter	ube
ALL DIMS IN	mm	DWG NO	13419	SHEET 1 OF 1