





FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING




BANDPASS FILTER

REV. 001	VALUE
CENTER WAVELENGTH (CWL)	266nm ±2nm
FULL WIDTH HALF MAX (FWHM)	10.0 ±2nm
MINIMUM TRANSMISSION	≥50%
BLOCKING	200 - 650nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	Hard Coated
DURABILITY	MIL-C-48497a, SEC 3.4.1
ENVIRONMENTAL	MIL-STD-810F, SEC 507.4


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY





THIRD ANGLE PROJECTION		TITLE	Filter BP 266 x 10nm OD4 25mm		
		DWG NO	39313	SHEET 1 OF 1	



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER



	VALUE
CENTER WAVELENGTH (nm)	355nm
FULL WIDTH HALF MAX (nm)	10nm
MINIMUM TRANSMISSION	≥85
BLOCKING	200 - 1200
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**



THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm


TITLE

OD4, Ø25mm, 355nm x 10nm, HC, BP FILTER


DWG NO

34491



SHEET  
1 OF 1



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
CENTER WAVELENGTH (nm)	532nm
FULL WIDTH HALF MAX (nm)	10nm
MINIMUM TRANSMISSION	≥85
BLOCKING	200 - 1200
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**



THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm


TITLE

OD4,  $\varnothing 25\text{mm}$ , 532nm x 10nm, HC, BP FILTER


DWG NO

65155



SHEET  
1 OF 1



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER



	VALUE
CENTER WAVELENGTH (nm)	1064nm
FULL WIDTH HALF MAX (nm)	10nm
MINIMUM TRANSMISSION	≥85
BLOCKING	200 - 1200
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics®**

THIRD ANGLE PROJECTION		TITLE	OD4, Ø25mm, 1064nm x 10nm, HC, BP FILTER		
		DWG NO	65187	SHEET	1 OF 1