


NOTES:




1. SUBSTRATE:
HOYA GLASS: ND-50
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <0.02 mm

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




3. FINE GRIND SURFACE

4. COATING SPECIFICATION:
S1 & S2:R(AVG) $\leq 0.5\%$ @ 600 - 1050nm
5. OPTICAL DENSITY: 0.2 +/-0.04 @400-700nm
6. TRANSMISSION (%): 63.0% AVERAGE FROM 400-700nm
7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®

| | | | | | | | |
|-----------------|----------------------|----------------------|---|----|--------|--|-----------------|
| | S1 | S2 | THIRD ANGLE PROJECTION  | | TITLE | 0.2 OD, 25mm DIA., NIR I COATED, ABSORPTIVE ND FILTER | |
| SHAPE | PLANO | PLANO | | | TITLE | | |
| SURFACE QUALITY | 80-50 | 80-50 | | | TITLE | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 13165 | SHEET 1 OF 1 |