






NOTES:

- 1. SUBSTRATE: D263
- 2. DIFFRACTION: 6° @ 915nm
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2:
R(ABS) < 0.5% @ 915nm
- 4. GROOVE DENSITY: 114 grooves/mm



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	TITLE	915nm Laser V-Coat, 25mm Square, 6° Diffraction Polarization Grating		
SURFACE QUALITY	60-40	60-40		DWG NO	16591		SHEET 1 OF 1
CLEAR APERTURE	Ø24.5	Ø24.5					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm			