



NOTES:

1. SUBSTRATE:
D-ZK3
2. NUMERICAL APERTURE:
OBJECT: 0.30
IMAGE: 0.30
WD, OBJECT (mm): 1.67
WD, IMAGE (mm): 1.67
3. COATING
S1 & S2: R(AVG) $\leq 0.5\%$ @ 350 - 700nm
4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
5. DESIGN WAVELENGTH: 980nm



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	1.16		Edmund Optics®
			BFL	0.51		
SHAPE	CONVEX	CONVEX	THIRD ANGLE PROJECTION		TITLE	LightPath 354450 1.8mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	16682
CLEAR APERTURE	$\varnothing 1.14$	$\varnothing 1.14$				SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				