



NOTES:

1. SUBSTRATE: L-BAL35
2. COATING
S1: NONE
S2: NONE
3. EDGES: FINE GROUND
4. CENTERING: 3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75 µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$

7. SOLD AS A PACK OF 10 x ASPHERIC LENS #17-082



COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	12.500000E+00
(1/RADIUS)	6.789788E-02
k	-1.439137E+00
D	0.000000E+00
E	3.416666E-05
F	-6.438044E-09
G	2.323731E-11
H	-3.519619E-14
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm : 25			
SHAPE	CONVEX	PLANO	BFL @ 587.6nm: 20.28			
RADIUS	14.728	INFINITY				
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	90%	90%	TITLE			
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	17156
					SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 **Edmund Optics®**

25mm Dia., 0.50 Numerical Aperture,
Uncoated, Precision Molded Aspheric Lens
(Pack of 10)