




NOTES:

1. MATERIAL: UV Grade Fused Silica
2. TRANSMITTED WAVEFRONT ERROR: $<\lambda/4$




	VALUE
CENTER WAVELENGTH (CWL)	520.00 .00 nm
TRANSMISSION BANDWIDTH (MINIMUM)	36.00 nm
FULL WIDTH HALF MAX (TYPICAL)	41.00 .00 nm
AVERAGE TRANSMISSION OVER BANDWITH (MINIMUM)	93 %
BLOCKING WAVELENGTH RANGE	250 - 1025 nm
OD6 BLOCKING RANGE < 3% FROM EDGE OF BANDWIDTH	250 - 488 & 560 - 700
CLEAR APERTURE (mm)	$\phi 22.50$
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A, SECTION 3.4.1
ENVIRONMENTAL	MIL-STD-810F, SECTION 507.4

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 	TITLE	520nm CWL, 25mm Dia, 36nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter	
	ALL DIMS IN	mm	DWG NO 18390