

NOTES:



- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:R(AVG) ≥78% @ 120 - 125nm  
R(AVG) ≥85% @ 120 - 600nm  
S2: COMMERCIAL POLISH

4. S2 & EDGES FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATION APPLY ACROSS CLEAR APERTURE

6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	N/A
SURFACE FLATNESS	λ/10	N/A
COATING TYPE	METAL	N/A
COATING	ENHANCED ALUMINUM (120-600nm)	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

		<div><div></div><div>Edmund Optics®</div></div>		
<div>THIRD ANGLE PROJECTION</div> <div></div>		TITLE	15mm Dia., Vacuum UV (VUV) Mirror	
ALL DIMS IN	mm	DWG NO	18727	SHEET 1 OF 1