







FOCAL LENGTH (EFL): 60 ±0,6
BACK FOCAL LENGTH (BFL): 57,48


SURFACE A			SURFACE B		SURFACE C			
Øe 14			Øe 14		Øe 14			
			CEMENT: NOA 61 OR EQUIVALENT					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					15mm Dia, x 60mm FL, VIS-NIR Coated, Achromatic Lens			
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	49954	SHEET SIZE A4	SHEET 1 OF 3



- 1 AR COATING: VIS-NIR
 $R(ABS) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 37,23±0,037 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BK7 517/642	R 26,69±0,027 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 15mm Dia, x 60mm FL, VIS-NIR Coated, Achromatic Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN:	mm			DWG NO 49954	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110								



- 1 AR COATING: VIS-NIR
 $R(ABS) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 26,69±0,027 CV Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF5 673/322	R 76,36±0,076 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 15mm Dia, x 60mm FL, VIS-NIR Coated, Achromatic Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm				DWG NO 49954	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110								