

NOTES:

1. SUBSTRATE:  
ZERODUR®
2. S2 TO BE PARALLEL TO S1 TO WITHIN 30 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: Enhanced Aluminum (250-700nm)  
 R(AVG) >89% @ 250 - 450nm  
 R(AVG) >85% @ 250 - 700nm  
 S2: NONE

4. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)

5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

7. ARROW ON EDGE POINTS TOWARDS 1/10TH WAVE SURFACE S1

8. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	COMMERCIAL POLISH
SURFACE FLATNESS	$\lambda/10$	N/A
CLEAR APERTURE	36.00 x 36.00	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN mm

**EO**® Edmund Optics®

TITLE 40 x 40mm UV-Enhanced Aluminum Coated,  
 $\lambda/10$  ZERODUR® Mirror

DWG NO 17784 SHEET 1 OF 1