



NOTES:

1. SUBSTRATE: Fused Silica
2. RoHS: COMPLIANT
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: R(ABS) > 99.80% @ 1064nm @ 0-45° AOI  
  
DAMAGE THRESHOLD PULSED: 15 J/cm<sup>2</sup> @ 20ns, 20Hz @ 1064nm  
  
S2 & S3: NONE

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	S3
SHAPE	PLANO	PLANO	PLANO
SURFACE QUALITY	10-5	FINE GRIND SURFACE	COMMERCIAL POLISH
CLEAR APERTURE	$\phi 22.5$	N/A	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

STEMMED LASER MIRROR,  $\phi 25$ mm, 1064nm

DWG NO

17555

SHEET  
1 OF 1