




NOTES:


1. SUBSTRATE: POLYMER FILM XP42-70
2. OPERATING TEMPERATURE (°C): -10 to +60
3. OPERATING HUMIDITY (%): ≤80 (No Condensation)
4. WAVELENGTH RANGE: 400-700nm
5. POLARIZATION: >99.98
6. TRANSMISSION (%):
 SINGLE 42 ±2
 PARALLEL: 36.4
 CROSSED: <0.004
7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	25mm Dia. Linear Polarizer (XP42-70)	
ALL DIMS IN	mm	DWG NO	19941	SHEET 1 OF 1