



NOTES:


1. SUBSTRATE: POLYMER FILM XP40HT-18
2. TEMPERTURE RESISTANCE (°C x HOURS):
 HEAT: 100 x 1,000
 COLD: -40 x 1,000
 HUMIDITY: 80 x 90% RH x 1,000
3. WAVELENGTH RANGE: 400 -700 nm
4. POLARIZATION EFFICIENCY (%): >99.5
5. TRANSMISSION (%):
 SINGLE: 40
 PARALLEL: 32.2
 CROSSED: <0.005
6. EXTINCTION RATIO: 5000:1
7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

THIRD ANGLE PROJECTION 		TITLE	50 x 50mm HIGH-TEMPERTURE LINEAR POLARIZING FILM (XP40HT-18)	
ALL DIMS IN	mm	DWG NO	13912	SHEET 1 OF 1