


NOTES:

1. ALLOWABLE OPTICAL MATERIAL:
OPTICAL GRADE SILICON
2. CENTERING TOLERANCE: <3 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:

R(AVG) <1% FROM 1650 TO 3000nm
R(ABS) <2% FROM 1650 TO 3000nm

4. FINE GRIND SURFACE



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

	S1	S2	EFL (AT 10.6 microns)	40.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO					
RADIUS	96.7	INFINITY					
SURFACE QUALITY	60 - 40	60 - 40	BFL (AT 10.6 microns)	39.12	TITLE	25mm Dia. x 40mm FL, BBAR (1650-3000nm) Coated, Si Plano-Convex Lens	
CLEAR APERTURE	ø24.00	ø24.00					
BEVEL MAX FACE	0.25 x 45°	0.25 x 45°	ALL DIMS IN	mm	DWG NO	21091	SHEET 1 OF 1