NOTES:

- 1. SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):


\$1, \$2, \$3, & \$4: R(AVG) <0.5% @ 430 - 670nm \$5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 25% ± 5%

POLARIZATION < 6%


FINE GROUND SURFACE

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

/6.\ MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

\$1		
	\$2	
SHAPE PLANO PLANO		
Surface accuracy $\lambda/8$		
SURFACE QUALITY 40-20 40-20		
CLEAR APERTURE > 90% > 90%		

			Edmund Option	S®
THIRD ANGLE -		TITLE	25mm VIS, 70R/30T, Non-Polarizing C Beamsplitter	ube
ALL DIMS IN	mm	DWG NO	13435	SHEET 1 OF 1