






NOTES:


1. SUBSTRATE:
HOYA GLASS: ND-40
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <0.02 mm
3.  FINE GRIND SURFACE
4. COATING SPECIFICATION:
S1 & S2:R(AVG) $\leq 0.4\%$ @ 425 - 675nm
5. OPTICAL DENSITY: 0.4 +/-0.05 @400-700nm
6. TRANSMISSION (%): 40.0% AVERAGE FROM 400-700nm
7. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



| | | | | | | | |
|-----------------|----------------------|----------------------|---|----|--------|---|-----------------|
| | S1 | S2 | THIRD ANGLE PROJECTION  | | TITLE | 0.4 OD, 12.5mm DIA., VIS 0° COATED, ABSORPTIVE ND FILTER | |
| SHAPE | PLANO | PLANO | | | | | |
| SURFACE QUALITY | 80-50 | 80-50 | | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 13082 | SHEET 1 OF 1 |