


NOTES:

1. SUBSTRATE: N-BK7
2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
2. COATING (APPLY ACROSS CLEAR APERTURE)



S1 & S2: R(ABS) ≤ 1.5% @ 750 - 800nm
 R(ABS) ≤ 1.0% @ 800 - 1550nm
 R(ABS) ≤ 0.7% @ 750 - 1550nm



4. FINE GRIND SURFACE

5. ROHS COMPLIANT

Ø 25.00^{0.00}_{-0.25}



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|-----------------|---------------------|---------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 60 - 40 | 60 - 40 |
| CLEAR APERTURE | Ø 22.50 | Ø 22.50 |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED |

THIRD ANGLE PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE

25mm Dia., 4mm Thick, NIR II Coated λ/4 N-BK7 Window

DWG NO

25806

SHEET 19 OF 36