



NOTES:

1. SUBSTRATE: CALCIUM FLUORIDE (CAF₂) VACUUM UV GRADE
2. SURFACE S1 TO BE PARALLEL WITH SURFACE S2 TO <1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: R(AVG) <1% @ 1650 - 3000nm
 R(ABS) <2% @ 1650 - 3000nm


4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNES	$\lambda/2$	$\lambda/2$
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	$\varnothing 11.43$	$\varnothing 11.43$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



EO® Edmund Optics®

TITLE	12.7mm Diameter, BBAR (1650-3000nm) Coated, Calcium Fluoride Window	
DWG NO	17604	SHEET 1 OF 1