




FOCAL LENGTH (EFL): 35 ±0,35
BACK FOCAL LENGTH (BFL): 29,17

1 VIS-EXT
R(AVG) ≤ 0,5% FROM 350 - 700nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 16,045 CX Øe 24 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 24 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION ALL DIMS IN: mm	Edmund Optics® TITLE 25mm Dia x 35mm FL, VIS-EXT Coated, Plano-Convex Lens DWG NO 26327 SHEET SIZE A4 SHEET 1 OF 1	