

NOTES:


1. SUBSTRATE:
NITROCELLULOSE

2. COATING (APPLY ACROSS CLEAR APERTURE)



S1: METAL/DIELECTRIC
40% R @ 400-700nm @ 45° AOI
40% T @ 400-700nm @ 45° AOI
R/T TOLERANCE: ±3%

S2: NONE

3. ROHS COMPLIANT



SECTION A-A



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø12.7	Ø12.7
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

12.7mm Clear Aperture 40R/40T, Pellicle
Beamsplitter

DWG NO

19308

SHEET
1 OF 1