





FOCAL LENGTH (EFL): 25 ±0,25
BACK FOCAL LENGTH (BFL): 22,09

- 1 NIR I
R(AVG) ≤ 0,5% FROM 600 - 1050nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 11,462 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 14				Øe 14		
SEE NOTE 1				SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 15mm Dia x 25mm FL, NIR I Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26335
					SHEET T SIZE	A4
					SHEET 1 OF 1	