




FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): 15,94

1 532nm V-COAT
 R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 8,25 CX Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®						
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE	9mm Dia x 18mm FL, 532NM V-COAT Coated, Plano-Convex Lens				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY										
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	mm	DWG NO	25868		SHEET T SIZE	A4	SHEET 1 OF
INDICATIONS IN ACCORDANCE WITH ISO 10110										