




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
BEAM DIVERGENCE (mrad)	3.5
COLOR	Infrared
OUTPUT POWER (mW)	50
POINT STABILITY AFTER WARM UP (mrad/°C)	<0.05
POLARIZATION	>50:1
POWER STABILITY (%)	<2% RMS over 4 hours
WAVELENGTH (nm)	808
MODULATION FREQUENCY (kHz)	1
BEAM DIAMETER (mm)	3.5

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®



THIRD ANGLE
PROJECTION

TITLE

Laser LC Turnkey 808nm x 50mW

ALL DIMS IN

mm

DWG NO

19489

SHEET
1 OF 1