





FOCAL LENGTH (EFL): 10 ±0,1
BACK FOCAL LENGTH (BFL): 8,63

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 4,585 CX Øe 4,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 4,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 6,55' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 5mm Dia x 10mm FL, 785NM V-COAT Coated, Plano-Convex Lens DWG NO 25895 SHEET SIZE A4 SHEET 1 OF 1	