




FOCAL LENGTH (EFL): 20 ±0,2
BACK FOCAL LENGTH (BFL): 18,97

1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 9,17 CX Øe 4,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 4,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING FIRST ANGLE PROJECTION Edmund Optics® 5mm Dia x 20mm FL, 785NM V-COAT Coated, Plano-Convex Lens TITLE DWG NO 25897 SHEET 1 OF 1		