





FOCAL LENGTH (EFL): 25 ± 0,25
BACK FOCAL LENGTH (BFL): 23,97

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R 11,46 CX			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL			
Øe 4,5					Øe 4,5			
SEE NOTE 1					SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm					3/ 3 (0,5) λ=632,8 nm			
4/ -					4/ 2,18'			
5/ 40 - 20					5/ 40 - 20			
6/ -			6/ -					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 5mm Dia x 25mm FL, 785NM V-COAT Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	25898	SHEET T SIZE A4	SHEET 1 OF 1