




NOTES:

1. SUBSTRATE:
CP42HE Laminated Between Glass
2. OPERATING TEMPERATURE: -40 to +80 °C
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS AR Coated
Ravg <0.5% @ 425 - 700nm
4. EFFICIENCY OF LINEAR COMPONENT: >99.90 %
5. WAVELENGTH RANGE: 425 - 700 nm
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION		TITLE	15mm Dia. Left-Handed VIS-Coated Glass Circular Polarizer (CP42HE)	
ALL DIMS IN	mm	DWG NO	19933	SHEET 1 OF 1