



NOTES:

1. SUBSTRATE: FUSED SILICA (CORNING 7980)
2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1 & S2: R(ABS) $\leq 0.25\%$ @ 880nm
 R(AVG) $\leq 1.25\%$ FROM 400 - 870nm
 R(AVG) $\leq 1.25\%$ FROM 890 - 1000nm
3. SURFACE S1 TO BE PARALLEL WITH SURFACE S2 TO WITHIN < 10 ARCSEC

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø 135.00	Ø 135.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE 150mm Dia., 8mm Thick, VIS-NIR Coated $\lambda/10$ Fused Silica Window

DWG NO 22072

SHEET 1 OF 1